




Universal Plus Headlamp

HDCU22



Consumers use headlamps for various activities. Whenever they need a light that provides hands-free operation, the Universal Plus Headlamp is a great option. It is compact and lightweight for optimal comfort. Its sleek design makes it a great light for outdoor activities and its bright light output is perfect for any indoor OR DIY project. This light is easy to use and provides 2 different light outputs, which includes a red light that helps to preserve night vision. The Universal Plus Headlamp features a durable construction and an adjustable head strap that makes it a versatile and dependable option. Compact, comfortable, dependable, and easy to use, the Universal Plus Headlamp is the perfect solution for any indoor or outdoor activity.

Lumens	Runtime	Beam Distance	Drop	Water Ingress
				
FL1 STANDARD	FL1 STANDARD	FL1 STANDARD	FL1 STANDARD	FL1 STANDARD



DESIGN BENEFITS
✓ Bright, compact and lightweight ✓ Easy-to-use push button ✓ Comfortable band that is removable and washable ✓ Durable construction ✓ Red LED for night vision

PERFORMANCE BENEFITS
✓ Up to 12x brighter vs standard LED technology ✓ Long run time ✓ 2 modes: High / Red (Night Vision)

LIGHT AND POWER SOURCE
✓ Features LED technology ✓ Operates on 2 AAA

BATTERY SPECIFICATIONS			
Battery Type	ENR Max Alkaline, ROV Alkaline HE		
Battery Size	AAA		
Number of Cells	2		
BATTERY PERFORMANCE			
Modes	Lumens (lm)	Runtime (h)	Beam Distance (m)
White	100	9	40

PRODUCT SPECIFICATIONS	
Weight:	39 Grams / 1.38 Ounces
Dimensions:	94 mm x 37 mm x 27 mm 3.70" x 1.45" x 1.06"

ELECTRICAL CHARACTERISTICS	
Nominal Power Consumption:	1.05 W
Batteries:	2 AAA Energizer E92 3.0V dc
LED Specifications:	LED 3.0V cc / 350 mA

BATTERY SPECIFICATIONS			
Battery Type	ENR SHD CZn, ROV CZn HD		
Battery Size	AAA		
Number of Cells	2		
BATTERY PERFORMANCE			
Modes	Lumens (lm)	Runtime (h)	Beam Distance (m)
White	60	8	30

DISCLAIMERS
Tested according to ANSI/NEMA FL1 Standards. This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

CERTIFICATES AND COMPLIANCE
EMC, EN62471, FCC
  

Modes
High, Red

OPERATING INSTRUCTIONS

1. Press 1 time for high.
2. Press 2 times for red.
3. Press again for off.

BATTERY CHANGING INSTRUCTIONS

1. Compress latch to open back battery door.
2. Follow instruction on light body for battery orientation.